

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294767

Luminaire Tested: P3AS09R65W2N902750DE010 E3D1WMH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3D1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 702.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294767
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294767

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	10.7
10°-20°	199.8	28.5
20°-30°	252.9	36.0
30°-40°	144.0	20.5
40°-50°	28.6	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	75.1
0°-40°	671.5	95.7
0°-60°	701.6	99.9
0°-90°	702.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	702.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	858	
5°	794	75
15°	717	200
25°	567	253
35°	229	144
45°	34	29
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294767
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	857.8
1°	851.5
2°	837.6
3°	821.5
4°	805.6
5°	793.5
6°	784.5
7°	777.3
8°	771.0
9°	764.6
10°	758.6
11°	751.9
12°	745.0
13°	736.6
14°	727.7
15°	717.0
16°	704.3
17°	690.5
18°	675.5
19°	659.6
20°	644.9
21°	629.9
22°	616.3
23°	602.2
24°	585.7
25°	566.7
26°	543.9
27°	516.5
28°	485.6
29°	452.7
30°	418.4
31°	380.6
32°	343.1
32.5°	323.7
33°	305.0
34°	266.9
35°	229.4
36°	194.8
37°	160.4
37.5°	142.8
38°	128.7
39°	104.2
40°	85.1
42.5°	52.5
45°	33.5



TEST NUMBER: P1294767
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.6
50°	7.2
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)