

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294788

Luminaire Tested: P3AS09R65W2N902750DE010 E3DL1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294788  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902750DE010 E3DL1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 366.0 lumens  
Efficiency: N/A  
Efficacy: 40.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294788  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294788

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93041
5°	90711
10°	84479
15°	75710
20°	65386
25°	54390
30°	42893
35°	31775
40°	21898
45°	13583
50°	7369
55°	4626
60°	3947
65°	3580
70°	3013
75°	2711
80°	2652
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13583 cd/sqm



TEST NUMBER: P1294788

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	10.5
10°-20°	92.7	25.3
20°-30°	102.5	28.0
30°-40°	74.4	20.3
40°-50°	34.9	9.5
50°-60°	11.7	3.2
60°-70°	6.8	1.9
70°-80°	3.5	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.5	63.8
0°-40°	307.9	84.1
0°-60°	354.5	96.9
0°-90°	366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	366.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	424	
5°	412	38
15°	334	93
25°	225	102
35°	119	74
45°	44	35
55°	12	12
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1294788

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	424.3
2.5°	421.6
5°	412.1
7.5°	397.9
10°	379.4
12.5°	357.8
15°	333.5
17.5°	307.1
20°	280.2
22.5°	252.2
25°	224.8
27.5°	196.8
30°	169.4
32.5°	143.0
35°	118.7
37.5°	96.6
40°	76.5
42.5°	58.6
45°	43.8
47.5°	31.7
50°	21.6
52.5°	14.8
55°	12.1
57.5°	10.6
60°	9.0
62.5°	7.9
65°	6.9
67.5°	5.8
70°	4.7
72.5°	4.2
75°	3.2
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)