

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294844

Luminaire Tested: P3AS09R65W2N902750DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3DLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 404.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294844
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294844
 CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102689
5°	100132
10°	93251
15°	83565
20°	72176
25°	60028
30°	47349
35°	35094
40°	24188
45°	14978
50°	8153
55°	5123
60°	4342
65°	3943
70°	3334
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14978 cd/sqm



TEST NUMBER: P1294844
 CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.3	10.5
10°-20°	102.3	25.3
20°-30°	113.1	28.0
30°-40°	82.2	20.3
40°-50°	38.5	9.5
50°-60°	12.9	3.2
60°-70°	7.5	1.9
70°-80°	3.9	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.7	63.8
0°-40°	339.9	84.1
0°-60°	391.3	96.9
0°-90°	404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	468	
5°	455	42
15°	368	102
25°	248	113
35°	131	82
45°	48	38
55°	13	13
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294844
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	468.3
2.5°	465.4
5°	454.9
7.5°	439.2
10°	418.8
12.5°	394.9
15°	368.1
17.5°	339.0
20°	309.3
22.5°	278.4
25°	248.1
27.5°	217.3
30°	187.0
32.5°	157.8
35°	131.1
37.5°	106.6
40°	84.5
42.5°	64.7
45°	48.3
47.5°	34.9
50°	23.9
52.5°	16.3
55°	13.4
57.5°	11.6
60°	9.9
62.5°	8.7
65°	7.6
67.5°	6.4
70°	5.2
72.5°	4.7
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)