

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292910

Luminaire Tested: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292910  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902750DE010 E3DL1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 378.0 lumens  
Efficiency: N/A  
Efficacy: 42.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292910  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292910

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121503
5°	118512
10°	108348
15°	91964
20°	72806
25°	55068
30°	40082
35°	27117
40°	16660
45°	9551
50°	5765
55°	4664
60°	4079
65°	3632
70°	3013
75°	2965
80°	2904
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9551 cd/sqm



TEST NUMBER: P1292910

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.8	13.2
10°-20°	111.7	29.5
20°-30°	104.5	27.6
30°-40°	63.9	16.9
40°-50°	25.2	6.7
50°-60°	11.1	2.9
60°-70°	6.9	1.8
70°-80°	3.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.9	70.3
0°-40°	329.8	87.3
0°-60°	366.1	96.9
0°-90°	378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	378.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	554	
5°	538	50
15°	405	112
25°	228	104
35°	101	64
45°	31	25
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1292910  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	554.1
1°	554.7
2°	552.9
3°	549.4
4°	544.2
5°	538.4
6°	530.8
7°	522.1
8°	511.6
9°	500.0
10°	486.6
11°	472.6
12°	457.5
13°	441.2
14°	423.1
15°	405.1
17.5°	358.5
20°	312.0
22.5°	267.1
25°	227.6
27.5°	190.9
30°	158.3
32.5°	128.0
35°	101.3
37.5°	77.4
40°	58.2
42.5°	41.9
45°	30.8
47.5°	22.1
50°	16.9
52.5°	14.0
55°	12.2
57.5°	10.5
60°	9.3
62.5°	8.1
65°	7.0
67.5°	5.8
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6



TEST NUMBER: P1292910  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)