

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292915

Luminaire Tested: P3AS09R35W2N902750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 612.9 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292915
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292915

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.8	20.0
10°-20°	238.0	38.8
20°-30°	155.8	25.4
30°-40°	63.2	10.3
40°-50°	19.0	3.1
50°-60°	6.4	1.1
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.6	84.3
0°-40°	579.8	94.6
0°-60°	605.2	98.7
0°-90°	612.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	612.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1410	
5°	1350	123
15°	874	238
25°	332	156
35°	96	63
45°	23	19
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1292915
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1409.9
1°	1407.6
2°	1401.2
3°	1388.4
4°	1373.2
5°	1349.9
6°	1320.7
7°	1288.1
8°	1251.3
9°	1209.3
10°	1162.7
11°	1110.8
12°	1056.6
13°	995.9
14°	938.2
15°	873.5
17.5°	716.6
20°	568.5
22.5°	437.3
25°	331.8
27.5°	247.2
30°	181.9
32.5°	133.5
35°	96.2
37.5°	68.2
40°	47.8
42.5°	33.2
45°	22.7
47.5°	15.2
50°	9.9
52.5°	7.6
55°	7.0
57.5°	6.4
60°	5.8
62.5°	5.2
65°	4.1
67.5°	3.5
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1292915
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)