

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292921

Luminaire Tested: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 235.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292921
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1292921
 CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53680
5°	52542
10°	49209
15°	44177
20°	38433
25°	32736
30°	27422
35°	21844
40°	15801
45°	9986
50°	5458
55°	3785
60°	3552
65°	3321
70°	3142
75°	2711
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9986 cd/sqm



TEST NUMBER: P1292921

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	9.5
10°-20°	54.2	23.0
20°-30°	62.1	26.4
30°-40°	50.6	21.5
40°-50°	25.5	10.9
50°-60°	9.5	4.0
60°-70°	6.4	2.7
70°-80°	3.5	1.5
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	138.4	58.9
0°-40°	189.0	80.4
0°-60°	224.1	95.3
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	245	
5°	239	22
15°	195	54
25°	135	62
35°	82	51
45°	32	26
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1292921
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	244.8
1°	244.5
2°	243.9
3°	242.8
4°	241.0
5°	238.7
6°	235.8
7°	232.9
8°	229.1
9°	225.3
10°	221.0
11°	216.3
12°	211.4
13°	205.9
14°	200.1
15°	194.6
17.5°	179.8
20°	164.7
22.5°	149.3
25°	135.3
27.5°	121.7
30°	108.3
32.5°	95.0
35°	81.6
37.5°	68.2
40°	55.2
42.5°	43.0
45°	32.2
47.5°	23.2
50°	16.0
52.5°	11.6
55°	9.9
57.5°	9.0
60°	8.1
62.5°	7.3
65°	6.4
67.5°	5.5
70°	4.9
72.5°	4.1
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.5
85°	0.9
87.5°	0.6



TEST NUMBER: P1292921
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)