

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294898

Luminaire Tested: P3AS09R65W2N902765DE010 E3D1H\_5000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1294898  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902765DE010 E3D1H\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 702.0 lumens  
Efficiency: N/A  
Efficacy: 78.0 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294898

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3D1H\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294898

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3D1H\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	188099
5°	174664
10°	168912
15°	162771
20°	150490
25°	137113
30°	105940
35°	61409
40°	24360
45°	10389
50°	2456
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10389 cd/sqm



TEST NUMBER: P1294898

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3D1H\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.8	10.7
10°-20°	199.8	28.5
20°-30°	252.9	36.0
30°-40°	144.0	20.5
40°-50°	28.6	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	75.1
0°-40°	671.5	95.7
0°-60°	701.6	99.9
0°-90°	702.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	702.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	858	
5°	794	75
15°	717	200
25°	567	253
35°	229	144
45°	34	29
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294898

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3D1H\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	857.8
1°	851.5
2°	837.6
3°	821.5
4°	805.6
5°	793.5
6°	784.5
7°	777.3
8°	771.0
9°	764.6
10°	758.6
11°	751.9
12°	745.0
13°	736.6
14°	727.7
15°	717.0
16°	704.3
17°	690.5
18°	675.5
19°	659.6
20°	644.9
21°	629.9
22°	616.3
23°	602.2
24°	585.7
25°	566.7
26°	543.9
27°	516.5
28°	485.6
29°	452.7
30°	418.4
31°	380.6
32°	343.1
32.5°	323.7
33°	305.0
34°	266.9
35°	229.4
36°	194.8
37°	160.4
37.5°	142.8
38°	128.7
39°	104.2
40°	85.1
42.5°	52.5
45°	33.5



TEST NUMBER: P1294898

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3D1H\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	19.6
50°	7.2
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)