

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294961

Luminaire Tested: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 225.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294961
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294961
 CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40041
5°	39511
10°	38187
15°	36005
20°	33206
25°	30147
30°	26688
35°	22727
40°	18091
45°	12746
50°	7403
55°	4052
60°	3772
65°	3424
70°	3142
75°	2881
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12746 cd/sqm



TEST NUMBER: P1294961
 CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.9	7.5
10°-20°	44.4	19.7
20°-30°	57.0	25.3
30°-40°	52.8	23.4
40°-50°	31.8	14.1
50°-60°	10.9	4.8
60°-70°	6.5	2.9
70°-80°	3.7	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.3	52.6
0°-40°	171.0	76.0
0°-60°	213.7	95.0
0°-90°	225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	183	
5°	180	17
15°	159	44
25°	125	57
35°	85	53
45°	41	32
55°	11	11
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1294961
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	182.6
2.5°	181.7
5°	179.5
7.5°	176.0
10°	171.5
12.5°	165.7
15°	158.6
17.5°	150.9
20°	142.3
22.5°	133.4
25°	124.6
27.5°	115.2
30°	105.4
32.5°	95.7
35°	84.9
37.5°	74.3
40°	63.2
42.5°	52.0
45°	41.1
47.5°	31.1
50°	21.7
52.5°	13.7
55°	10.6
57.5°	9.4
60°	8.6
62.5°	7.4
65°	6.6
67.5°	5.7
70°	4.9
72.5°	4.3
75°	3.4
77.5°	2.9
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)