

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293036

Luminaire Tested: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293036  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 272.0 lumens  
Efficiency: N/A  
Efficacy: 30.2 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293036  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293036

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	137182
5°	131851
10°	114872
15°	87991
20°	58875
25°	35615
30°	20434
35°	11430
40°	6069
45°	3132
50°	1501
55°	1185
60°	1140
65°	934
70°	1026
75°	847
80°	1010
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3132 cd/sqm



TEST NUMBER: P1293036

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	20.0
10°-20°	105.6	38.8
20°-30°	69.1	25.4
30°-40°	28.0	10.3
40°-50°	8.4	3.1
50°-60°	2.9	1.1
60°-70°	1.9	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.2	84.3
0°-40°	257.3	94.6
0°-60°	268.5	98.7
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	626	
5°	599	54
15°	388	106
25°	147	69
35°	43	28
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293036  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	625.6
1°	624.6
2°	621.7
3°	616.0
4°	609.3
5°	599.0
6°	586.0
7°	571.5
8°	555.2
9°	536.6
10°	515.9
11°	492.9
12°	468.8
13°	441.9
14°	416.3
15°	387.6
17.5°	318.0
20°	252.3
22.5°	194.0
25°	147.2
27.5°	109.7
30°	80.7
32.5°	59.2
35°	42.7
37.5°	30.3
40°	21.2
42.5°	14.7
45°	10.1
47.5°	6.7
50°	4.4
52.5°	3.4
55°	3.1
57.5°	2.8
60°	2.6
62.5°	2.3
65°	1.8
67.5°	1.6
70°	1.6
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3



TEST NUMBER: P1293036  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1GPH\_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)