

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295037

Luminaire Tested: P3AS09R70W2N902750DE010 E3CB1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902750DE010 E3CB1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 661.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295037
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3CB1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1295037

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3CB1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	8.1
10°-20°	143.6	21.7
20°-30°	200.6	30.3
30°-40°	186.0	28.1
40°-50°	66.7	10.1
50°-60°	5.6	0.9
60°-70°	2.8	0.4
70°-80°	1.8	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.4	60.1
0°-40°	583.3	88.3
0°-60°	655.7	99.2
0°-90°	661.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	599	
5°	569	53
15°	511	144
25°	437	201
35°	308	186
45°	80	67
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1295037
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	598.6
2.5°	589.6
5°	569.0
7.5°	550.0
10°	535.2
12.5°	523.0
15°	510.9
17.5°	496.1
20°	478.7
22.5°	458.6
25°	436.9
27.5°	414.7
30°	388.3
32.5°	354.5
35°	308.5
37.5°	249.9
40°	186.0
42.5°	126.8
45°	79.8
47.5°	44.4
50°	19.0
52.5°	6.3
55°	4.2
57.5°	3.7
60°	3.7
62.5°	3.2
65°	2.6
67.5°	2.6
70°	2.1
72.5°	2.1
75°	1.6
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)