

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293066

Luminaire Tested: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293066  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 555.0 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293066  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293066  
 CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	279912
5°	269029
10°	234398
15°	179524
20°	120107
25°	72682
30°	41703
35°	23316
40°	12395
45°	6388
50°	3070
55°	2409
60°	2324
65°	1920
70°	2052
75°	1779
80°	2020
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6388 cd/sqm



TEST NUMBER: P1293066

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.2	20.0
10°-20°	215.5	38.8
20°-30°	141.1	25.4
30°-40°	57.2	10.3
40°-50°	17.2	3.1
50°-60°	5.8	1.1
60°-70°	3.9	0.7
70°-80°	2.3	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.7	84.3
0°-40°	525.0	94.6
0°-60°	548.0	98.7
0°-90°	555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	555.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1276	
5°	1222	111
15°	791	215
25°	300	141
35°	87	57
45°	21	17
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1293066  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1276.5
1°	1274.4
2°	1268.6
3°	1257.0
4°	1243.3
5°	1222.2
6°	1195.8
7°	1166.2
8°	1132.9
9°	1094.9
10°	1052.7
11°	1005.7
12°	956.6
13°	901.7
14°	849.4
15°	790.8
17.5°	648.8
20°	514.7
22.5°	395.9
25°	300.4
27.5°	223.8
30°	164.7
32.5°	120.9
35°	87.1
37.5°	61.8
40°	43.3
42.5°	30.1
45°	20.6
47.5°	13.7
50°	9.0
52.5°	6.9
55°	6.3
57.5°	5.8
60°	5.3
62.5°	4.8
65°	3.7
67.5°	3.2
70°	3.2
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5



TEST NUMBER: P1293066  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DL1WMH\_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)