

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293077

Luminaire Tested: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 233.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293077
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293077

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53219
5°	52102
10°	48786
15°	43791
20°	38107
25°	32470
30°	27194
35°	21656
40°	15658
45°	9924
50°	5390
55°	3747
60°	3552
65°	3269
70°	3142
75°	2711
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9924 cd/sqm



TEST NUMBER: P1293077

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.0	9.5
10°-20°	53.7	23.0
20°-30°	61.5	26.4
30°-40°	50.2	21.6
40°-50°	25.3	10.9
50°-60°	9.4	4.0
60°-70°	6.3	2.7
70°-80°	3.5	1.5
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	137.2	58.9
0°-40°	187.4	80.4
0°-60°	222.1	95.3
0°-90°	233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	243	
5°	237	22
15°	193	54
25°	134	62
35°	81	50
45°	32	25
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1293077

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	242.7
1°	242.4
2°	241.9
3°	240.7
4°	239.0
5°	236.7
6°	233.8
7°	230.9
8°	227.2
9°	223.4
10°	219.1
11°	214.5
12°	209.6
13°	204.1
14°	198.4
15°	192.9
17.5°	178.2
20°	163.3
22.5°	148.0
25°	134.2
27.5°	120.6
30°	107.4
32.5°	94.2
35°	80.9
37.5°	67.7
40°	54.7
42.5°	42.6
45°	32.0
47.5°	23.0
50°	15.8
52.5°	11.5
55°	9.8
57.5°	8.9
60°	8.1
62.5°	7.2
65°	6.3
67.5°	5.5
70°	4.9
72.5°	4.0
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.6



TEST NUMBER: P1293077
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)