

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295069

Luminaire Tested: P3AS09R70W2N902750DE010 E3D1LI\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295069  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R70W2N902750DE010 E3D1LI\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 706.1 lumens  
Efficiency: N/A  
Efficacy: 78.5 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295069  
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3D1LI\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295069

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3D1LI\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	137270
5°	129430
10°	122732
15°	120523
20°	116187
25°	109506
30°	108726
35°	94710
40°	61258
45°	28964
50°	4060
55°	344
60°	263
65°	311
70°	192
75°	254
80°	379
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28964 cd/sqm



TEST NUMBER: P1295069

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3D1LI\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.9	7.8
10°-20°	149.1	21.1
20°-30°	210.9	29.9
30°-40°	212.0	30.0
40°-50°	76.3	10.8
50°-60°	2.1	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.9	58.8
0°-40°	626.9	88.8
0°-60°	705.2	99.9
0°-90°	706.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	626	
5°	588	55
15°	531	149
25°	453	211
35°	354	212
45°	93	76
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1295069

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3D1LI\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	626.0
1°	624.3
2°	618.8
3°	610.1
4°	599.1
5°	588.0
6°	577.6
7°	569.5
8°	562.2
9°	556.4
10°	551.2
11°	546.9
12°	542.8
13°	538.8
14°	535.0
15°	530.9
16°	526.0
17°	520.8
18°	514.4
19°	506.6
20°	497.9
21°	488.3
22°	478.7
23°	469.5
24°	460.5
25°	452.6
26°	447.1
27°	442.8
28°	439.3
29°	435.2
30°	429.4
31°	421.0
32°	409.1
32.5°	402.5
33°	393.5
34°	375.8
35°	353.8
36°	329.4
37°	301.9
37.5°	289.1
38°	271.7
39°	240.7
40°	214.0
42.5°	148.2
45°	93.4



TEST NUMBER: P1295069

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3D1LI\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	50.2
50°	11.9
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)