

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295104

Luminaire Tested: P3AS09R70W2N902750DE010 E3DL1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902750DE010 E3DL1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 596.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295104
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DL1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295104

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DL1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	8.2
10°-20°	130.7	21.9
20°-30°	169.9	28.5
30°-40°	144.1	24.2
40°-50°	74.3	12.5
50°-60°	14.3	2.4
60°-70°	7.8	1.3
70°-80°	4.8	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.3	58.6
0°-40°	493.5	82.8
0°-60°	582.1	97.7
0°-90°	596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	518	49
15°	467	131
25°	373	170
35°	232	144
45°	96	74
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1295104
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DL1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	526.2
2.5°	524.4
5°	517.9
7.5°	508.4
10°	497.2
12.5°	483.0
15°	467.0
17.5°	447.5
20°	425.6
22.5°	400.7
25°	372.9
27.5°	341.5
30°	307.8
32.5°	270.5
35°	232.0
37.5°	194.1
40°	158.0
42.5°	124.3
45°	95.9
47.5°	70.4
50°	40.8
52.5°	17.8
55°	11.2
57.5°	10.7
60°	9.5
62.5°	8.9
65°	7.7
67.5°	7.1
70°	5.9
72.5°	5.3
75°	4.7
77.5°	3.6
80°	3.0
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)