

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293114

Luminaire Tested: P3AS09R35W2N902765DE010 E3DLP1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902765DE010 E3DLP1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 343.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293114
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293114
 CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | 93 | 93 | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | 94 | 92 | 89 | 91 | 89 | 87 | 86 | 86 | 86 | 86 |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | 89 | 85 | 82 | 86 | 84 | 81 | 80 | 80 | 80 | 80 |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 82 | 78 | 86 | 81 | 77 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | 74 | 74 | 74 |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | 69 | 69 | 69 |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | 65 | 65 | 65 |
| 7 | 83 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 61 | 61 | 61 | 61 |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | 57 | 57 | 57 |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | 54 | 54 | 54 |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 | 51 | 51 | 51 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 110254 |
| 5° | 107528 |
| 10° | 98306 |
| 15° | 83451 |
| 20° | 66062 |
| 25° | 49963 |
| 30° | 36385 |
| 35° | 24601 |
| 40° | 15114 |
| 45° | 8683 |
| 50° | 5219 |
| 55° | 4244 |
| 60° | 3728 |
| 65° | 3269 |
| 70° | 2693 |
| 75° | 2711 |
| 80° | 2652 |
| 85° | 2768 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8683 cd/sqm



TEST NUMBER: P1293114

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1H_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 45.1 | 13.2 |
| 10°-20° | 101.3 | 29.5 |
| 20°-30° | 94.8 | 27.6 |
| 30°-40° | 58.0 | 16.9 |
| 40°-50° | 22.9 | 6.7 |
| 50°-60° | 10.1 | 2.9 |
| 60°-70° | 6.3 | 1.8 |
| 70°-80° | 3.3 | 1.0 |
| 80°-90° | 1.2 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 241.3 | 70.3 |
| 0°-40° | 299.3 | 87.3 |
| 0°-60° | 332.2 | 96.9 |
| 0°-90° | 343.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 343.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 503 | |
| 5° | 488 | 45 |
| 15° | 368 | 101 |
| 25° | 206 | 95 |
| 35° | 92 | 58 |
| 45° | 28 | 23 |
| 55° | 11 | 10 |
| 65° | 6 | 6 |
| 75° | 3 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1293114
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1H_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 502.8 |
| 1° | 503.3 |
| 2° | 501.7 |
| 3° | 498.6 |
| 4° | 493.8 |
| 5° | 488.5 |
| 6° | 481.7 |
| 7° | 473.7 |
| 8° | 464.2 |
| 9° | 453.7 |
| 10° | 441.5 |
| 11° | 428.8 |
| 12° | 415.1 |
| 13° | 400.3 |
| 14° | 383.9 |
| 15° | 367.6 |
| 17.5° | 325.3 |
| 20° | 283.1 |
| 22.5° | 242.4 |
| 25° | 206.5 |
| 27.5° | 173.2 |
| 30° | 143.7 |
| 32.5° | 116.2 |
| 35° | 91.9 |
| 37.5° | 70.2 |
| 40° | 52.8 |
| 42.5° | 38.0 |
| 45° | 28.0 |
| 47.5° | 20.1 |
| 50° | 15.3 |
| 52.5° | 12.7 |
| 55° | 11.1 |
| 57.5° | 9.5 |
| 60° | 8.5 |
| 62.5° | 7.4 |
| 65° | 6.3 |
| 67.5° | 5.3 |
| 70° | 4.2 |
| 72.5° | 3.7 |
| 75° | 3.2 |
| 77.5° | 2.6 |
| 80° | 2.1 |
| 82.5° | 1.6 |
| 85° | 1.1 |
| 87.5° | 0.5 |



TEST NUMBER: P1293114
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1H_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)