

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293130

Luminaire Tested: P3AS09R35W2N902765DE010 E3DLP1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902765DE010 E3DLP1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 382.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293130
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293130
 CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	13.2
10°-20°	112.9	29.5
20°-30°	105.6	27.6
30°-40°	64.6	16.9
40°-50°	25.5	6.7
50°-60°	11.2	2.9
60°-70°	7.0	1.8
70°-80°	3.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.7	70.3
0°-40°	333.3	87.3
0°-60°	370.0	96.9
0°-90°	382.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	544	50
15°	409	113
25°	230	106
35°	102	65
45°	31	25
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293130
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	559.9
1°	560.5
2°	558.8
3°	555.2
4°	549.9
5°	544.1
6°	536.4
7°	527.6
8°	517.0
9°	505.2
10°	491.7
11°	477.6
12°	462.3
13°	445.8
14°	427.6
15°	409.4
17.5°	362.3
20°	315.3
22.5°	270.0
25°	230.0
27.5°	192.9
30°	160.0
32.5°	129.4
35°	102.3
37.5°	78.2
40°	58.8
42.5°	42.3
45°	31.2
47.5°	22.4
50°	17.1
52.5°	14.1
55°	12.4
57.5°	10.6
60°	9.4
62.5°	8.2
65°	7.1
67.5°	5.9
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6



TEST NUMBER: P1293130
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)