

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295188

Luminaire Tested: P3AS09R70W2N902765DE010 E3CD1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295188  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R70W2N902765DE010 E3CD1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,  
E3CD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 729.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295188  
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295188

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53	53	53	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144769
5°	138124
10°	131416
15°	127901
20°	123187
25°	116595
30°	108447
35°	91096
40°	58710
45°	27290
50°	7164
55°	1797
60°	1798
65°	1505
70°	1475
75°	1440
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27290 cd/sqm



TEST NUMBER: P1295188

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.7	8.1
10°-20°	158.3	21.7
20°-30°	221.2	30.3
30°-40°	205.1	28.1
40°-50°	73.5	10.1
50°-60°	6.3	0.9
60°-70°	3.1	0.4
70°-80°	2.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.3	60.1
0°-40°	643.4	88.3
0°-60°	723.1	99.2
0°-90°	729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	729.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	660	
5°	628	59
15°	563	158
25°	482	221
35°	340	205
45°	88	74
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1295188  
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	660.2
2.5°	650.3
5°	627.5
7.5°	606.6
10°	590.2
12.5°	576.8
15°	563.4
17.5°	547.1
20°	527.9
22.5°	505.8
25°	481.9
27.5°	457.4
30°	428.3
32.5°	391.0
35°	340.3
37.5°	275.6
40°	205.1
42.5°	139.8
45°	88.0
47.5°	48.9
50°	21.0
52.5°	7.0
55°	4.7
57.5°	4.1
60°	4.1
62.5°	3.5
65°	2.9
67.5°	2.9
70°	2.3
72.5°	2.3
75°	1.7
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)