

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295213

Luminaire Tested: P3AS09R70W2N902765DE010 E3D1WH_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRIS
Catalog Number: P3AS09R70W2N902765DE010 E3D1WH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 706.1 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295213
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295213
 CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137270
5°	129430
10°	122732
15°	120523
20°	116187
25°	109506
30°	108726
35°	94710
40°	61258
45°	28964
50°	4060
55°	344
60°	263
65°	311
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28964 cd/sqm



TEST NUMBER: P1295213

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	7.8
10°-20°	149.1	21.1
20°-30°	210.9	29.9
30°-40°	212.0	30.0
40°-50°	76.3	10.8
50°-60°	2.1	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.9	58.8
0°-40°	626.9	88.8
0°-60°	705.2	99.9
0°-90°	706.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	626	
5°	588	55
15°	531	149
25°	453	211
35°	354	212
45°	93	76
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1295213
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	626.0
1°	624.3
2°	618.8
3°	610.1
4°	599.1
5°	588.0
6°	577.6
7°	569.5
8°	562.2
9°	556.4
10°	551.2
11°	546.9
12°	542.8
13°	538.8
14°	535.0
15°	530.9
16°	526.0
17°	520.8
18°	514.4
19°	506.6
20°	497.9
21°	488.3
22°	478.7
23°	469.5
24°	460.5
25°	452.6
26°	447.1
27°	442.8
28°	439.3
29°	435.2
30°	429.4
31°	421.0
32°	409.1
32.5°	402.5
33°	393.5
34°	375.8
35°	353.8
36°	329.4
37°	301.9
37.5°	289.1
38°	271.7
39°	240.7
40°	214.0
42.5°	148.2
45°	93.4



TEST NUMBER: P1295213
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WH_3500K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	50.2
50°	11.9
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)