

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293178

Luminaire Tested: P3AS09R40W2N902750DE010 E3CD1MB\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293178  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902750DE010 E3CD1MB\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 819.0 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293178  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3CD1MB\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293178

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3CD1MB\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92	92	92	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89	89	89	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85	85	85	85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82	82	82	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79	79	79	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76	76	76	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73	73	73	73
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69	69	69	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	431215
5°	429143
10°	415156
15°	367312
20°	239654
25°	84900
30°	18003
35°	5916
40°	2176
45°	713
50°	580
55°	650
60°	526
65°	623
70°	385
75°	508
80°	758
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 1008 cd/sqm



TEST NUMBER: P1293178

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3CD1MB\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.4	22.4
10°-20°	427.2	52.2
20°-30°	185.4	22.6
30°-40°	17.1	2.1
40°-50°	2.4	0.3
50°-60°	1.5	0.2
60°-70°	1.1	0.1
70°-80°	0.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	796.1	97.2
0°-40°	813.1	99.3
0°-60°	817.0	99.8
0°-90°	819.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	819.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1966	
5°	1950	183
15°	1618	427
25°	351	185
35°	22	17
45°	2	2
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293178  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3CD1MB\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1966.5
2.5°	1964.2
5°	1949.6
7.5°	1918.7
10°	1864.5
12.5°	1773.0
15°	1618.0
17.5°	1361.0
20°	1027.0
22.5°	666.8
25°	350.9
27.5°	151.0
30°	71.1
32.5°	38.5
35°	22.1
37.5°	13.4
40°	7.6
42.5°	4.1
45°	2.3
47.5°	1.7
50°	1.7
52.5°	1.7
55°	1.7
57.5°	1.7
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)