

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295309

Luminaire Tested: P3AS13R15W2N902750DE010 E3CB1MB_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15W2N902750DE010 E3CB1MB_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 981.1 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295309
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3CB1MB_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295309

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3CB1MB_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98 | | |
| 2 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 | 102 | 101 | 99 | 99 | 98 | 97 | 96 | | |
| 3 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 100 | 102 | 100 | 98 | 100 | 98 | 97 | 98 | 97 | 95 | 94 | | |
| 4 | 107 | 103 | 100 | 97 | 106 | 102 | 99 | 97 | 100 | 97 | 95 | 98 | 96 | 94 | 97 | 95 | 93 | 92 | | |
| 5 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 92 | 91 | | |
| 6 | 103 | 98 | 94 | 92 | 102 | 97 | 94 | 92 | 96 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 90 | 89 | | |
| 7 | 101 | 96 | 92 | 90 | 100 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 91 | 89 | 92 | 90 | 89 | 88 | | |
| 8 | 99 | 94 | 90 | 88 | 98 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 89 | 87 | 91 | 89 | 87 | 86 | | |
| 9 | 97 | 92 | 89 | 87 | 97 | 92 | 89 | 86 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 86 | 85 | | |
| 10 | 96 | 90 | 87 | 85 | 95 | 90 | 87 | 85 | 89 | 87 | 85 | 89 | 86 | 85 | 88 | 86 | 85 | 84 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1906821 |
| 5° | 1598103 |
| 10° | 752781 |
| 15° | 226948 |
| 20° | 83984 |
| 25° | 32663 |
| 30° | 12179 |
| 35° | 3748 |
| 40° | 1345 |
| 45° | 713 |
| 50° | 546 |
| 55° | 612 |
| 60° | 702 |
| 65° | 415 |
| 70° | 513 |
| 75° | 678 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm



TEST NUMBER: P1295309

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3CB1MB_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 561.3 | 57.2 |
| 10°-20° | 333.6 | 34.0 |
| 20°-30° | 70.1 | 7.1 |
| 30°-40° | 11.3 | 1.2 |
| 40°-50° | 1.9 | 0.2 |
| 50°-60° | 1.4 | 0.1 |
| 60°-70° | 0.9 | 0.1 |
| 70°-80° | 0.5 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 965.0 | 98.4 |
| 0°-40° | 976.3 | 99.5 |
| 0°-60° | 979.7 | 99.9 |
| 0°-90° | 981.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 981.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 8696 | |
| 5° | 7260 | 561 |
| 15° | 1000 | 334 |
| 25° | 135 | 70 |
| 35° | 14 | 11 |
| 45° | 2 | 2 |
| 55° | 2 | 1 |
| 65° | 1 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1295309
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3CB1MB_3500K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 8695.8 |
| 1° | 8668.7 |
| 2° | 8530.6 |
| 3° | 8254.5 |
| 4° | 7849.7 |
| 5° | 7260.2 |
| 6° | 6567.6 |
| 7° | 5775.8 |
| 8° | 5019.6 |
| 9° | 4163.3 |
| 10° | 3380.8 |
| 12.5° | 1824.2 |
| 15° | 999.7 |
| 17.5° | 585.6 |
| 20° | 359.9 |
| 22.5° | 220.3 |
| 25° | 135.0 |
| 27.5° | 81.4 |
| 30° | 48.1 |
| 32.5° | 27.1 |
| 35° | 14.0 |
| 37.5° | 7.8 |
| 40° | 4.7 |
| 42.5° | 3.1 |
| 45° | 2.3 |
| 47.5° | 1.6 |
| 50° | 1.6 |
| 52.5° | 1.6 |
| 55° | 1.6 |
| 57.5° | 1.6 |
| 60° | 1.6 |
| 62.5° | 0.8 |
| 65° | 0.8 |
| 67.5° | 0.8 |
| 70° | 0.8 |
| 72.5° | 0.8 |
| 75° | 0.8 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)