

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295388

Luminaire Tested: P3AS13R15W2N902750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15W2N902750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 793.0 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295388
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295388
 CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	677424
5°	601319
10°	417583
15°	246948
20°	140642
25°	80400
30°	44488
35°	23718
40°	13110
45°	7102
50°	4435
55°	3517
60°	3026
65°	2750
70°	2436
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7102 cd/sqm



TEST NUMBER: P1295388

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.3	29.3
10°-20°	306.6	38.7
20°-30°	157.9	19.9
30°-40°	59.3	7.5
40°-50°	19.4	2.4
50°-60°	8.3	1.1
60°-70°	5.3	0.7
70°-80°	3.1	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.7	87.9
0°-40°	756.0	95.3
0°-60°	783.7	98.8
0°-90°	793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3089	
5°	2732	232
15°	1088	307
25°	332	158
35°	89	59
45°	23	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1295388
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3089.3
1°	3083.2
2°	3042.7
3°	2965.6
4°	2864.0
5°	2731.8
6°	2582.1
7°	2417.8
8°	2235.3
9°	2055.0
10°	1875.4
12.5°	1443.1
15°	1087.8
17.5°	814.3
20°	602.7
22.5°	450.0
25°	332.3
27.5°	242.2
30°	175.7
32.5°	124.5
35°	88.6
37.5°	63.4
40°	45.8
42.5°	32.8
45°	22.9
47.5°	16.8
50°	13.0
52.5°	10.7
55°	9.2
57.5°	7.6
60°	6.9
62.5°	6.1
65°	5.3
67.5°	4.6
70°	3.8
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)