

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295392

Luminaire Tested: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 268.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295392
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1295392
 CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	70	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67604
5°	65771
10°	60097
15°	52645
20°	45154
25°	37696
30°	30182
35°	22620
40°	16431
45°	10730
50°	6720
55°	4549
60°	4035
65°	3684
70°	3462
75°	3135
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10730 cd/sqm



TEST NUMBER: P1295392

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.6	10.3
10°-20°	64.6	24.1
20°-30°	71.2	26.6
30°-40°	53.3	19.9
40°-50°	27.6	10.3
50°-60°	11.5	4.3
60°-70°	7.1	2.6
70°-80°	4.0	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.4	61.0
0°-40°	216.7	80.9
0°-60°	255.8	95.4
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	308	
5°	299	28
15°	232	65
25°	156	71
35°	84	53
45°	35	28
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1295392
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	308.3
1°	308.6
2°	307.6
3°	305.6
4°	302.5
5°	298.8
6°	294.0
7°	288.9
8°	282.8
9°	276.4
10°	269.9
12.5°	251.2
15°	231.9
17.5°	212.5
20°	193.5
22.5°	174.2
25°	155.8
27.5°	137.5
30°	119.2
32.5°	101.2
35°	84.5
37.5°	70.3
40°	57.4
42.5°	45.5
45°	34.6
47.5°	26.1
50°	19.7
52.5°	14.6
55°	11.9
57.5°	10.5
60°	9.2
62.5°	8.1
65°	7.1
67.5°	6.1
70°	5.4
72.5°	4.4
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3
90°	0.0

(END OF REPORT)