

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293352

Luminaire Tested: P3AS09R40W2N902765DE010 E3D1LI\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902765DE010 E3D1LI\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 829.0 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293352  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1LI\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293352

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1LI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	422554
5°	419501
10°	408521
15°	364928
20°	241964
25°	90658
30°	24257
35°	9476
40°	3406
45°	1613
50°	512
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1613 cd/sqm



TEST NUMBER: P1293352

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1LI\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.8	21.7
10°-20°	425.9	51.4
20°-30°	193.2	23.3
30°-40°	25.0	3.0
40°-50°	4.3	0.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.9	96.4
0°-40°	824.0	99.4
0°-60°	828.8	100.0
0°-90°	829.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	829.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1927	
5°	1906	180
15°	1608	426
25°	375	193
35°	35	25
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1293352

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1LI\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1927.0
1°	1925.9
2°	1923.0
3°	1918.6
4°	1913.1
5°	1905.8
6°	1897.4
7°	1887.0
8°	1874.2
9°	1856.8
10°	1834.7
11°	1808.9
12°	1774.4
13°	1731.7
14°	1676.0
15°	1607.5
16°	1520.1
17°	1420.6
18°	1301.0
19°	1174.8
20°	1036.9
21°	899.1
22°	763.3
23°	628.0
24°	495.1
25°	374.7
26°	277.4
27°	203.2
28°	152.7
29°	118.7
30°	95.8
31°	79.2
32°	66.2
32.5°	60.4
33°	54.6
34°	44.4
35°	35.4
36°	27.9
37°	22.1
37.5°	19.7
38°	17.4
39°	14.5
40°	11.9
42.5°	7.8
45°	5.2



TEST NUMBER: P1293352  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1LI\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	3.2
50°	1.5
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)