

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295413

Luminaire Tested: P3AS13R15W2N902750DE010 E3DLD1WH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295413  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902750DE010 E3DLD1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 602.9 lumens  
Efficiency: N/A  
Efficacy: 49.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295413  
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1WH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1295413

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	10.3
10°-20°	145.4	24.1
20°-30°	160.2	26.6
30°-40°	119.9	19.9
40°-50°	62.2	10.3
50°-60°	25.8	4.3
60°-70°	16.0	2.6
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.6	61.0
0°-40°	487.5	80.9
0°-60°	575.4	95.4
0°-90°	602.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	694	
5°	672	62
15°	522	145
25°	351	160
35°	190	120
45°	78	62
55°	27	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1295413  
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	693.6
1°	694.4
2°	692.1
3°	687.5
4°	680.6
5°	672.2
6°	661.5
7°	650.1
8°	636.3
9°	621.8
10°	607.3
12.5°	565.3
15°	521.7
17.5°	478.2
20°	435.4
22.5°	391.9
25°	350.6
27.5°	309.4
30°	268.1
32.5°	227.6
35°	190.2
37.5°	158.1
40°	129.1
42.5°	102.4
45°	77.9
47.5°	58.8
50°	44.3
52.5°	32.8
55°	26.7
57.5°	23.7
60°	20.6
62.5°	18.3
65°	16.0
67.5°	13.8
70°	12.2
72.5°	9.9
75°	8.4
77.5°	6.9
80°	5.3
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)