

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293373

Luminaire Tested: P3AS09R40W2N902765DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902765DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 302.0 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293373
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293373

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	77	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133630
5°	129760
10°	117744
15°	97276
20°	70169
25°	43406
30°	23497
35°	12153
40°	6612
45°	3690
50°	1842
55°	1376
60°	1272
65°	1193
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3690 cd/sqm



TEST NUMBER: P1293373

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	18.0
10°-20°	116.7	38.6
20°-30°	83.3	27.6
30°-40°	30.7	10.2
40°-50°	9.6	3.2
50°-60°	3.4	1.1
60°-70°	2.3	0.8
70°-80°	1.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.3	84.2
0°-40°	284.9	94.3
0°-60°	297.9	98.6
0°-90°	302.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	302.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	609	
5°	590	54
15°	428	117
25°	179	83
35°	45	31
45°	12	10
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293373
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	609.4
2.5°	604.7
5°	589.5
7.5°	564.1
10°	528.8
12.5°	484.0
15°	428.5
17.5°	366.3
20°	300.7
22.5°	236.1
25°	179.4
27.5°	131.7
30°	92.8
32.5°	65.1
35°	45.4
37.5°	32.1
40°	23.1
42.5°	16.6
45°	11.9
47.5°	8.0
50°	5.4
52.5°	3.9
55°	3.6
57.5°	3.4
60°	2.9
62.5°	2.6
65°	2.3
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)