

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293378

Luminaire Tested: P3AS09R40W2N902765DE010 E3DL1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902765DE010 E3DL1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 336.0 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293378
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293378

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148672
5°	144354
10°	130993
15°	108219
20°	78057
25°	48293
30°	26131
35°	13518
40°	7357
45°	4124
50°	2081
55°	1529
60°	1403
65°	1349
70°	1282
75°	1186
80°	1137
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4124 cd/sqm



TEST NUMBER: P1293378

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.5	18.0
10°-20°	129.8	38.6
20°-30°	92.6	27.6
30°-40°	34.1	10.2
40°-50°	10.8	3.2
50°-60°	3.7	1.1
60°-70°	2.6	0.8
70°-80°	1.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.9	84.2
0°-40°	317.0	94.3
0°-60°	331.5	98.6
0°-90°	336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	656	60
15°	477	130
25°	200	93
35°	50	34
45°	13	11
55°	4	4
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1293378
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	678.0
2.5°	672.8
5°	655.8
7.5°	627.6
10°	588.3
12.5°	538.4
15°	476.7
17.5°	407.5
20°	334.5
22.5°	262.7
25°	199.6
27.5°	146.5
30°	103.2
32.5°	72.4
35°	50.5
37.5°	35.8
40°	25.7
42.5°	18.5
45°	13.3
47.5°	8.9
50°	6.1
52.5°	4.3
55°	4.0
57.5°	3.7
60°	3.2
62.5°	2.9
65°	2.6
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)