

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293384

Luminaire Tested: P3AS09R40W2N902765DE010 E3DL1H\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293384  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902765DE010 E3DL1H\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 685.0 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293384  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1H\_6500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293384

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1H\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.2	18.0
10°-20°	264.6	38.6
20°-30°	188.9	27.6
30°-40°	69.5	10.2
40°-50°	21.9	3.2
50°-60°	7.6	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	576.8	84.2
0°-40°	646.3	94.4
0°-60°	675.7	98.7
0°-90°	685.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1382	
5°	1337	123
15°	972	265
25°	407	189
35°	103	70
45°	27	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1293384  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DL1H\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1382.3
2.5°	1371.7
5°	1337.0
7.5°	1279.4
10°	1199.4
12.5°	1097.7
15°	971.9
17.5°	830.8
20°	682.0
22.5°	535.6
25°	406.9
27.5°	298.7
30°	210.5
32.5°	147.6
35°	102.9
37.5°	72.9
40°	52.3
42.5°	37.6
45°	27.0
47.5°	18.2
50°	12.3
52.5°	8.8
55°	8.2
57.5°	7.6
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	2.9
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)