

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295454

Luminaire Tested: P3AS13R15W2N902750DE010 E3PH1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295454
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15W2N902750DE010 E3PH1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 663.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295454
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3PH1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295454
 CATALOG NUMBER: P3AS13R15W2N902750DE010 E3PH1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101	101	100	99
2	113	110	108	106	111	109	107	105	106	104	103		103	102	100		100	99	98	97
3	111	107	104	102	109	106	103	101	104	101	100		101	100	98		99	98	97	96
4	109	104	101	99	107	103	101	99	102	99	98		100	98	97		98	97	95	94
5	107	102	99	97	105	101	99	96	100	98	96		99	96	95		97	96	94	93
6	105	100	97	95	104	100	97	95	98	96	94		97	95	93		96	94	93	92
7	103	98	95	93	102	98	95	93	97	94	93		96	94	92		95	93	92	91
8	101	97	94	92	101	96	94	92	96	93	91		95	93	91		94	92	91	90
9	100	95	92	90	99	95	92	90	94	92	90		94	91	90		93	91	90	89
10	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92	90	89	88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1397892
5°	1212015
10°	589301
15°	125721
20°	26416
25°	7863
30°	1696
35°	294
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1295454
 CATALOG NUMBER: P3AS13R15W2N902750DE010 E3PH1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.1	64.9
10°-20°	213.9	32.3
20°-30°	17.8	2.7
30°-40°	1.2	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.8	99.8
0°-40°	663.0	100.0
0°-60°	663.0	100.0
0°-90°	663.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	663.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6375	
5°	5506	430
15°	554	214
25°	32	18
35°	1	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1295454
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3PH1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	6374.9
2.5°	6151.8
5°	5506.2
7.5°	4215.9
10°	2646.6
12.5°	1273.4
15°	553.8
17.5°	282.5
20°	113.2
22.5°	56.0
25°	32.5
27.5°	16.8
30°	6.7
32.5°	2.2
35°	1.1
37.5°	1.1
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)