

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293503

Luminaire Tested: P3AS09R45W2N902750DE010 E3CD1MMS\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3CD1MMS\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,  
E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 793.1 lumens  
Efficiency: N/A  
Efficacy: 88.1 lumens/watt  
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293503  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293503

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.1	18.7
10°-20°	339.9	42.9
20°-30°	244.7	30.9
30°-40°	50.9	6.4
40°-50°	4.7	0.6
50°-60°	1.9	0.2
60°-70°	1.6	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	732.7	92.4
0°-40°	783.7	98.8
0°-60°	790.3	99.6
0°-90°	793.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1568	
5°	1570	148
15°	1237	340
25°	540	245
35°	65	51
45°	4	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293503  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1567.9
2.5°	1568.5
5°	1570.3
7.5°	1559.0
10°	1504.6
12.5°	1391.1
15°	1236.7
17.5°	1078.8
20°	919.7
22.5°	736.9
25°	540.0
27.5°	356.0
30°	214.7
32.5°	120.1
35°	65.1
37.5°	36.7
40°	18.9
42.5°	8.3
45°	3.5
47.5°	2.4
50°	2.4
52.5°	2.4
55°	2.4
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)