

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293519

Luminaire Tested: P3AS09R45W2N902750DE010 E3DL1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3DL1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 324.0 lumens  
Efficiency: N/A  
Efficacy: 36.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293519  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1GPH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293519

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.0	15.4
10°-20°	111.9	34.5
20°-30°	95.1	29.3
30°-40°	45.4	14.0
40°-50°	13.7	4.2
50°-60°	3.5	1.1
60°-70°	2.6	0.8
70°-80°	1.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.0	79.3
0°-40°	302.3	93.3
0°-60°	319.5	98.6
0°-90°	324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	324.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	555	
5°	540	50
15°	408	112
25°	208	95
35°	70	45
45°	16	14
55°	4	3
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1293519  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	554.9
2.5°	551.4
5°	539.8
7.5°	519.8
10°	490.5
12.5°	451.7
15°	407.7
17.5°	358.7
20°	307.7
22.5°	255.9
25°	207.5
27.5°	163.4
30°	124.9
32.5°	93.9
35°	69.5
37.5°	51.3
40°	36.8
42.5°	25.5
45°	16.5
47.5°	9.3
50°	5.2
52.5°	4.1
55°	3.8
57.5°	3.5
60°	3.2
62.5°	2.9
65°	2.6
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)