

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293546

Luminaire Tested: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 225.0 lumens  
Efficiency: N/A  
Efficacy: 25.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293546  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293546

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	47715
5°	46863
10°	44332
15°	40432
20°	35750
25°	31066
30°	26662
35°	22218
40°	16545
45°	10141
50°	4674
55°	3670
60°	3508
65°	3217
70°	3013
75°	2881
80°	2652
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10141 cd/sqm



TEST NUMBER: P1293546

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.9	8.8
10°-20°	49.6	22.0
20°-30°	58.9	26.2
30°-40°	51.2	22.8
40°-50°	25.7	11.4
50°-60°	8.9	4.0
60°-70°	6.2	2.8
70°-80°	3.5	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.4	57.1
0°-40°	179.6	79.8
0°-60°	214.2	95.2
0°-90°	225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	225.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	218	
5°	213	20
15°	178	50
25°	128	59
35°	83	51
45°	33	26
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1293546  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	217.6
2.5°	216.5
5°	212.9
7.5°	207.2
10°	199.1
12.5°	189.3
15°	178.1
17.5°	165.7
20°	153.2
22.5°	140.5
25°	128.4
27.5°	116.7
30°	105.3
32.5°	94.4
35°	83.0
37.5°	70.8
40°	57.8
42.5°	45.1
45°	32.7
47.5°	21.5
50°	13.7
52.5°	10.6
55°	9.6
57.5°	8.8
60°	8.0
62.5°	7.3
65°	6.2
67.5°	5.4
70°	4.7
72.5°	3.9
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.6
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)