

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293548

Luminaire Tested: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293548  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 252.0 lumens  
Efficiency: N/A  
Efficacy: 28.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293548  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293548

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53439
5°	52476
10°	49654
15°	45290
20°	40043
25°	34792
30°	29853
35°	24869
40°	18549
45°	11350
50°	5254
55°	4091
60°	3947
65°	3632
70°	3334
75°	3219
80°	2904
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11350 cd/sqm



TEST NUMBER: P1293548

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.3	8.8
10°-20°	55.5	22.0
20°-30°	66.0	26.2
30°-40°	57.3	22.8
40°-50°	28.8	11.4
50°-60°	10.0	4.0
60°-70°	7.0	2.8
70°-80°	3.9	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.8	57.1
0°-40°	201.2	79.8
0°-60°	239.9	95.2
0°-90°	252.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	252.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	244	
5°	238	22
15°	200	56
25°	144	66
35°	93	57
45°	37	29
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293548  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	243.7
2.5°	242.5
5°	238.4
7.5°	232.0
10°	223.0
12.5°	212.0
15°	199.5
17.5°	185.6
20°	171.6
22.5°	157.4
25°	143.8
27.5°	130.7
30°	117.9
32.5°	105.7
35°	92.9
37.5°	79.3
40°	64.8
42.5°	50.5
45°	36.6
47.5°	24.1
50°	15.4
52.5°	11.9
55°	10.7
57.5°	9.9
60°	9.0
62.5°	8.1
65°	7.0
67.5°	6.1
70°	5.2
72.5°	4.4
75°	3.8
77.5°	2.9
80°	2.3
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)