

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295665

Luminaire Tested: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,  
E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 965.0 lumens  
Efficiency: N/A  
Efficacy: 78.5 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295665  
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295665  
 CATALOG NUMBER: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	96	95	93
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	86	84	82	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1498761
5°	1300877
10°	803793
15°	279184
20°	85734
25°	30316
30°	11217
35°	4497
40°	2405
45°	961
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 961 cd/sqm



TEST NUMBER: P1295665  
 CATALOG NUMBER: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	490.5	50.8
10°-20°	389.2	40.3
20°-30°	67.4	7.0
30°-40°	12.3	1.3
40°-50°	2.8	0.3
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.0	98.1
0°-40°	959.3	99.4
0°-60°	963.4	99.8
0°-90°	965.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6835	
5°	5910	490
15°	1230	389
25°	125	67
35°	17	12
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1295665  
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3CB1MMS\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6834.9
1°	6802.0
2°	6672.2
3°	6463.6
4°	6219.2
5°	5909.9
6°	5555.4
7°	5143.0
8°	4673.2
9°	4145.4
10°	3609.9
12.5°	2277.0
15°	1229.8
17.5°	656.9
20°	367.4
22.5°	210.1
25°	125.3
27.5°	76.4
30°	44.3
32.5°	26.0
35°	16.8
37.5°	11.5
40°	8.4
42.5°	5.3
45°	3.1
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)