

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293555

Luminaire Tested: P3AS09R45W2N902750DE010 E3DLD1H\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293555  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3DLD1H\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,  
E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 510.0 lumens  
Efficiency: N/A  
Efficacy: 56.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293555  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1H\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293555

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1H\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75			75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47			47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	108127
5°	106207
10°	100510
15°	91669
20°	81067
25°	70383
30°	60414
35°	50353
40°	37527
45°	22979
50°	10644
55°	8296
60°	7982
65°	7316
70°	6796
75°	6439
80°	5935
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22979 cd/sqm



TEST NUMBER: P1293555

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1H\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	8.8
10°-20°	112.4	22.0
20°-30°	133.6	26.2
30°-40°	116.1	22.8
40°-50°	58.2	11.4
50°-60°	20.2	4.0
60°-70°	14.2	2.8
70°-80°	7.9	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.1	57.1
0°-40°	407.1	79.8
0°-60°	485.6	95.2
0°-90°	510.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	510.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	493	
5°	482	45
15°	404	112
25°	291	134
35°	188	116
45°	74	58
55°	22	20
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1293555  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLD1H\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	493.1
2.5°	490.8
5°	482.5
7.5°	469.6
10°	451.4
12.5°	429.1
15°	403.8
17.5°	375.6
20°	347.4
22.5°	318.6
25°	290.9
27.5°	264.5
30°	238.6
32.5°	213.9
35°	188.1
37.5°	160.5
40°	131.1
42.5°	102.3
45°	74.1
47.5°	48.8
50°	31.2
52.5°	24.1
55°	21.7
57.5°	20.0
60°	18.2
62.5°	16.5
65°	14.1
67.5°	12.3
70°	10.6
72.5°	8.8
75°	7.6
77.5°	5.9
80°	4.7
82.5°	3.5
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)