

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295743

Luminaire Tested: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 298.0 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295743
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295743

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 91 | | | 91 |
| 2 | 106 | 100 | 96 | 92 | 104 | 99 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 90 | 87 | 85 | 83 | | | 83 |
| 3 | 100 | 93 | 87 | 82 | 98 | 91 | 86 | 82 | 88 | 84 | 80 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | | | 76 |
| 4 | 94 | 86 | 79 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | 70 |
| 5 | 89 | 80 | 73 | 68 | 87 | 79 | 73 | 68 | 77 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | | | 65 |
| 6 | 84 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 61 | 60 | | | 60 |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 60 | 57 | 55 | | | 55 |
| 8 | 75 | 65 | 59 | 54 | 74 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 53 | 61 | 57 | 53 | 52 | | | 52 |
| 9 | 72 | 61 | 55 | 50 | 70 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 48 | | | 48 |
| 10 | 68 | 58 | 51 | 47 | 67 | 57 | 51 | 47 | 56 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 45 | | | 45 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 73700 |
| 5° | 71737 |
| 10° | 65997 |
| 15° | 58093 |
| 20° | 49821 |
| 25° | 41857 |
| 30° | 33828 |
| 35° | 25752 |
| 40° | 18320 |
| 45° | 12094 |
| 50° | 7505 |
| 55° | 4932 |
| 60° | 4473 |
| 65° | 4099 |
| 70° | 3911 |
| 75° | 3558 |
| 80° | 3283 |
| 85° | 2768 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12094 cd/sqm



TEST NUMBER: P1295743

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 30.2 | 10.1 |
| 10°-20° | 71.2 | 23.9 |
| 20°-30° | 79.1 | 26.5 |
| 30°-40° | 60.3 | 20.2 |
| 40°-50° | 30.9 | 10.4 |
| 50°-60° | 12.7 | 4.3 |
| 60°-70° | 7.9 | 2.7 |
| 70°-80° | 4.4 | 1.5 |
| 80°-90° | 1.3 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 180.5 | 60.6 |
| 0°-40° | 240.8 | 80.8 |
| 0°-60° | 284.4 | 95.4 |
| 0°-90° | 298.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 298.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 336 | |
| 5° | 326 | 30 |
| 15° | 256 | 71 |
| 25° | 173 | 79 |
| 35° | 96 | 60 |
| 45° | 39 | 31 |
| 55° | 13 | 13 |
| 65° | 8 | 8 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1295743
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 336.1 |
| 1° | 336.5 |
| 2° | 335.0 |
| 3° | 333.1 |
| 4° | 330.1 |
| 5° | 325.9 |
| 6° | 321.0 |
| 7° | 315.7 |
| 8° | 310.0 |
| 9° | 303.2 |
| 10° | 296.4 |
| 12.5° | 276.7 |
| 15° | 255.9 |
| 17.5° | 234.7 |
| 20° | 213.5 |
| 22.5° | 192.3 |
| 25° | 173.0 |
| 27.5° | 153.7 |
| 30° | 133.6 |
| 32.5° | 114.7 |
| 35° | 96.2 |
| 37.5° | 79.9 |
| 40° | 64.0 |
| 42.5° | 50.3 |
| 45° | 39.0 |
| 47.5° | 29.5 |
| 50° | 22.0 |
| 52.5° | 16.3 |
| 55° | 12.9 |
| 57.5° | 11.7 |
| 60° | 10.2 |
| 62.5° | 9.1 |
| 65° | 7.9 |
| 67.5° | 6.8 |
| 70° | 6.1 |
| 72.5° | 4.9 |
| 75° | 4.2 |
| 77.5° | 3.4 |
| 80° | 2.6 |
| 82.5° | 1.9 |
| 85° | 1.1 |
| 87.5° | 0.4 |
| 90° | 0.0 |

(END OF REPORT)