

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295783

Luminaire Tested: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 531.0 lumens
Efficiency: N/A
Efficacy: 43.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295783
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295783

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	87	85	82	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	80	77	74	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	70	65	62	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	65	60	57	55
7	76	66	59	54	75	65	58	53	64	58	53	62	57	53	61	56	53	61	56	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	57	53	49	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	54	49	46	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	51	46	43	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150580
5°	139885
10°	118457
15°	92736
20°	72993
25°	58165
30°	46792
35°	38146
40°	31545
45°	26576
50°	22788
55°	19574
60°	17104
65°	14995
70°	12823
75°	11353
80°	8461
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26576 cd/sqm



TEST NUMBER: P1295783

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	10.8
10°-20°	114.4	21.5
20°-30°	111.0	20.9
30°-40°	89.7	16.9
40°-50°	66.7	12.6
50°-60°	46.3	8.7
60°-70°	29.0	5.5
70°-80°	14.1	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.8	53.3
0°-40°	372.5	70.2
0°-60°	485.5	91.4
0°-90°	531.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	531.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	636	57
15°	408	114
25°	240	111
35°	142	90
45°	86	67
55°	51	46
65°	29	29
75°	13	14
85°	2	2
90°	0	



TEST NUMBER: P1295783
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	686.7
2.5°	671.2
5°	635.5
7.5°	587.7
10°	532.0
12.5°	470.8
15°	408.5
17.5°	357.3
20°	312.8
22.5°	273.8
25°	240.4
27.5°	211.5
30°	184.8
32.5°	162.5
35°	142.5
37.5°	124.7
40°	110.2
42.5°	96.8
45°	85.7
47.5°	75.7
50°	66.8
52.5°	59.0
55°	51.2
57.5°	44.5
60°	39.0
62.5°	34.5
65°	28.9
67.5°	24.5
70°	20.0
72.5°	16.7
75°	13.4
77.5°	10.0
80°	6.7
82.5°	3.3
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)