

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295785

Luminaire Tested: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 373.9 lumens
Efficiency: N/A
Efficacy: 30.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295785
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295785

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	51	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132994
5°	124059
10°	102937
15°	78706
20°	59085
25°	44470
30°	32891
35°	22995
40°	15744
45°	10916
50°	9381
55°	9252
60°	9648
65°	9703
70°	9873
75°	10252
80°	11113
85°	11070

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 12936 cd/sqm



TEST NUMBER: P1295785

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	13.5
10°-20°	96.4	25.8
20°-30°	84.8	22.7
30°-40°	54.7	14.6
40°-50°	29.0	7.8
50°-60°	21.8	5.8
60°-70°	18.5	5.0
70°-80°	13.1	3.5
80°-90°	5.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.7	62.0
0°-40°	286.5	76.6
0°-60°	337.3	90.2
0°-90°	373.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	373.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	606	
5°	564	50
15°	347	96
25°	184	85
35°	86	55
45°	35	29
55°	24	22
65°	19	19
75°	12	13
85°	4	5
90°	0	



TEST NUMBER: P1295785
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3PHLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	606.5
2.5°	594.4
5°	563.6
7.5°	516.3
10°	462.3
12.5°	402.9
15°	346.7
17.5°	296.1
20°	253.2
22.5°	216.9
25°	183.8
27.5°	155.2
30°	129.9
32.5°	106.8
35°	85.9
37.5°	69.3
40°	55.0
42.5°	44.0
45°	35.2
47.5°	30.8
50°	27.5
52.5°	25.3
55°	24.2
57.5°	23.1
60°	22.0
62.5°	19.8
65°	18.7
67.5°	17.6
70°	15.4
72.5°	14.3
75°	12.1
77.5°	11.0
80°	8.8
82.5°	7.7
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)