

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293717

Luminaire Tested: P3AS09R45W2N902765DE010 E3DLD1WMH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293717  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902765DE010 E3DLD1WMH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 513.0 lumens  
Efficiency: N/A  
Efficacy: 57.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293717  
CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLD1WMH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293717

CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLD1WMH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.3	8.8
10°-20°	113.1	22.0
20°-30°	134.3	26.2
30°-40°	116.7	22.8
40°-50°	58.5	11.4
50°-60°	20.3	4.0
60°-70°	14.3	2.8
70°-80°	8.0	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.8	57.1
0°-40°	409.5	79.8
0°-60°	488.4	95.2
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	496	
5°	485	45
15°	406	113
25°	293	134
35°	189	117
45°	74	59
55°	22	20
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1293717

CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLD1WMH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	496.0
2.5°	493.7
5°	485.4
7.5°	472.4
10°	454.0
12.5°	431.6
15°	406.2
17.5°	377.8
20°	349.4
22.5°	320.4
25°	292.6
27.5°	266.0
30°	240.0
32.5°	215.2
35°	189.2
37.5°	161.4
40°	131.8
42.5°	102.9
45°	74.5
47.5°	49.1
50°	31.3
52.5°	24.2
55°	21.9
57.5°	20.1
60°	18.3
62.5°	16.6
65°	14.2
67.5°	12.4
70°	10.6
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.5
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)