

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295885

Luminaire Tested: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 267.0 lumens
Efficiency: N/A
Efficacy: 21.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295885
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1295885

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66047
5°	64275
10°	59139
15°	52055
20°	44641
25°	37502
30°	30308
35°	23048
40°	16402
45°	10823
50°	6720
55°	4396
60°	4035
65°	3684
70°	3462
75°	3135
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10823 cd/sqm



TEST NUMBER: P1295885

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.0	10.1
10°-20°	63.8	23.9
20°-30°	70.8	26.5
30°-40°	54.0	20.2
40°-50°	27.7	10.4
50°-60°	11.4	4.3
60°-70°	7.1	2.6
70°-80°	4.0	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.7	60.6
0°-40°	215.7	80.8
0°-60°	254.8	95.4
0°-90°	267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	267.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	301	
5°	292	27
15°	229	64
25°	155	71
35°	86	54
45°	35	28
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1295885
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	301.2
1°	301.5
2°	300.2
3°	298.5
4°	295.8
5°	292.0
6°	287.6
7°	282.9
8°	277.8
9°	271.7
10°	265.6
12.5°	247.9
15°	229.3
17.5°	210.3
20°	191.3
22.5°	172.3
25°	155.0
27.5°	137.7
30°	119.7
32.5°	102.8
35°	86.1
37.5°	71.6
40°	57.3
42.5°	45.1
45°	34.9
47.5°	26.5
50°	19.7
52.5°	14.6
55°	11.5
57.5°	10.5
60°	9.2
62.5°	8.1
65°	7.1
67.5°	6.1
70°	5.4
72.5°	4.4
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3
90°	0.0

(END OF REPORT)