

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293778

Luminaire Tested: P3AS09R50W2N902750DE010 E3CD1MMS_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50W2N902750DE010 E3CD1MMS_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 810.1 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293778
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3CD1MMS_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293778

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3CD1MMS_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 118.1 | 14.6 |
| 10°-20° | 298.7 | 36.9 |
| 20°-30° | 299.1 | 36.9 |
| 30°-40° | 84.1 | 10.4 |
| 40°-50° | 5.1 | 0.6 |
| 50°-60° | 1.9 | 0.2 |
| 60°-70° | 1.6 | 0.2 |
| 70°-80° | 1.0 | 0.1 |
| 80°-90° | 0.4 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 715.9 | 88.4 |
| 0°-40° | 800.0 | 98.8 |
| 0°-60° | 807.1 | 99.6 |
| 0°-90° | 810.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 810.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1286 | |
| 5° | 1259 | 118 |
| 15° | 1074 | 299 |
| 25° | 681 | 299 |
| 35° | 108 | 84 |
| 45° | 3 | 5 |
| 55° | 2 | 2 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 1 | 0 |
| 90° | 0 | |



TEST NUMBER: P1293778
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3CD1MMS_3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1286.5 |
| 2.5° | 1280.0 |
| 5° | 1258.6 |
| 7.5° | 1229.6 |
| 10° | 1194.7 |
| 12.5° | 1142.0 |
| 15° | 1074.5 |
| 17.5° | 997.0 |
| 20° | 921.8 |
| 22.5° | 828.2 |
| 25° | 681.4 |
| 27.5° | 507.4 |
| 30° | 354.0 |
| 32.5° | 213.7 |
| 35° | 107.7 |
| 37.5° | 50.9 |
| 40° | 23.7 |
| 42.5° | 8.9 |
| 45° | 3.0 |
| 47.5° | 2.4 |
| 50° | 2.4 |
| 52.5° | 2.4 |
| 55° | 2.4 |
| 57.5° | 1.8 |
| 60° | 1.8 |
| 62.5° | 1.8 |
| 65° | 1.8 |
| 67.5° | 1.2 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 1.2 |
| 77.5° | 0.6 |
| 80° | 0.6 |
| 82.5° | 0.6 |
| 85° | 0.6 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)