

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293800

Luminaire Tested: P3AS09R50W2N902750DE010 E3D1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50W2N902750DE010 E3D1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 805.1 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293800
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3D1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293800

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3D1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	14.6
10°-20°	296.8	36.9
20°-30°	297.3	36.9
30°-40°	83.6	10.4
40°-50°	5.0	0.6
50°-60°	1.9	0.2
60°-70°	1.6	0.2
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.5	88.4
0°-40°	795.1	98.8
0°-60°	802.1	99.6
0°-90°	805.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	805.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1278	
5°	1251	117
15°	1068	297
25°	677	297
35°	107	84
45°	3	5
55°	2	2
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1293800
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3D1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1278.5
2.5°	1272.1
5°	1250.9
7.5°	1222.0
10°	1187.3
12.5°	1135.0
15°	1067.9
17.5°	990.8
20°	916.1
22.5°	823.1
25°	677.2
27.5°	504.2
30°	351.8
32.5°	212.4
35°	107.1
37.5°	50.6
40°	23.5
42.5°	8.8
45°	2.9
47.5°	2.4
50°	2.4
52.5°	2.4
55°	2.4
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)