

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293856

Luminaire Tested: P3AS09R50W2N902750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50W2N902750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 463.0 lumens
Efficiency: N/A
Efficacy: 51.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293856
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293856
 CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	8.5
10°-20°	100.8	21.8
20°-30°	122.4	26.4
30°-40°	103.8	22.4
40°-50°	53.9	11.7
50°-60°	19.5	4.2
60°-70°	13.4	2.9
70°-80°	7.3	1.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.7	56.7
0°-40°	366.5	79.2
0°-60°	439.9	95.0
0°-90°	463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	463.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	429	
5°	421	39
15°	361	101
25°	268	122
35°	167	104
45°	70	54
55°	21	19
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1293856
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	429.1
2.5°	427.5
5°	421.2
7.5°	411.6
10°	397.9
12.5°	380.5
15°	361.4
17.5°	339.8
20°	316.0
22.5°	291.7
25°	267.9
27.5°	243.1
30°	217.7
32.5°	192.3
35°	167.0
37.5°	142.1
40°	117.3
42.5°	93.5
45°	69.8
47.5°	46.5
50°	30.1
52.5°	23.3
55°	21.1
57.5°	19.0
60°	17.4
62.5°	15.3
65°	13.7
67.5°	11.6
70°	10.0
72.5°	8.5
75°	6.9
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)