

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295967

Luminaire Tested: P3AS13R25W2N902750DE010 E3CD1MMS_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295967
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3CD1MMS_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 987.1 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295967
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3CD1MMS_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295967

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3CD1MMS_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.1	39.6
10°-20°	466.6	47.3
20°-30°	105.2	10.7
30°-40°	17.1	1.7
40°-50°	3.1	0.3
50°-60°	1.7	0.2
60°-70°	1.5	0.2
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	962.9	97.5
0°-40°	979.9	99.3
0°-60°	984.7	99.8
0°-90°	987.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	987.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4812	
5°	4446	391
15°	1676	467
25°	206	105
35°	20	17
45°	3	3
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1295967
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3CD1MMS_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4812.3
1°	4804.6
2°	4765.8
3°	4694.4
4°	4586.7
5°	4446.3
6°	4278.8
7°	4097.4
8°	3889.5
9°	3662.3
10°	3408.8
11°	3116.4
12°	2779.9
13°	2427.9
14°	2050.2
15°	1676.5
17.5°	955.3
20°	535.8
22.5°	323.4
25°	205.5
27.5°	126.4
30°	73.7
32.5°	38.8
35°	20.2
37.5°	13.2
40°	8.5
42.5°	5.4
45°	3.1
47.5°	2.3
50°	2.3
52.5°	2.3
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1295967
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3CD1MMS_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)