

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293886

Luminaire Tested: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293886  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 390.0 lumens  
Efficiency: N/A  
Efficacy: 43.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293886  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293886

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113434
5°	110367
10°	101779
15°	89512
20°	74883
25°	59374
30°	43576
35°	29955
40°	19036
45°	10637
50°	5765
55°	4855
60°	4166
65°	3840
70°	3398
75°	3135
80°	2652
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10637 cd/sqm



TEST NUMBER: P1293886

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	11.9
10°-20°	109.2	28.0
20°-30°	111.7	28.6
30°-40°	70.8	18.2
40°-50°	28.2	7.2
50°-60°	11.4	2.9
60°-70°	7.3	1.9
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.3	68.6
0°-40°	338.2	86.7
0°-60°	377.8	96.9
0°-90°	390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	517	
5°	501	46
15°	394	109
25°	245	112
35°	112	71
45°	34	28
55°	13	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293886  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	517.3
2.5°	513.6
5°	501.4
7.5°	482.4
10°	457.1
12.5°	427.0
15°	394.3
17.5°	358.4
20°	320.9
22.5°	283.5
25°	245.4
27.5°	207.4
30°	172.1
32.5°	140.4
35°	111.9
37.5°	87.6
40°	66.5
42.5°	49.1
45°	34.3
47.5°	23.2
50°	16.9
52.5°	14.3
55°	12.7
57.5°	11.1
60°	9.5
62.5°	8.4
65°	7.4
67.5°	6.3
70°	5.3
72.5°	4.2
75°	3.7
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)