

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293962

Luminaire Tested: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293962  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902765DE010 E3D1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 810.0 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293962  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293962

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	283069
5°	275522
10°	262921
15°	238026
20°	205935
25°	168929
30°	97028
35°	30142
40°	8101
45°	2822
50°	682
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2822 cd/sqm



TEST NUMBER: P1293962

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.2	14.5
10°-20°	290.5	35.9
20°-30°	305.4	37.7
30°-40°	87.4	10.8
40°-50°	8.5	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.1	88.0
0°-40°	800.5	98.8
0°-60°	809.7	100.0
0°-90°	810.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	810.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1291	
5°	1252	117
15°	1048	291
25°	698	305
35°	113	87
45°	9	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1293962  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1290.9
1°	1288.9
2°	1283.2
3°	1274.9
4°	1263.7
5°	1251.7
6°	1238.9
7°	1225.1
8°	1212.3
9°	1197.4
10°	1180.8
11°	1161.7
12°	1139.7
13°	1112.3
14°	1082.5
15°	1048.5
16°	1012.5
17°	977.7
18°	941.9
19°	910.5
20°	882.5
21°	855.6
22°	825.0
23°	789.9
24°	748.7
25°	698.2
26°	643.3
27°	582.1
28°	521.3
29°	455.5
30°	383.2
31°	315.5
32°	253.2
32.5°	226.1
33°	198.6
34°	152.3
35°	112.6
36°	82.6
37°	61.4
37.5°	53.2
38°	46.0
39°	35.7
40°	28.3
42.5°	16.0
45°	9.1



TEST NUMBER: P1293962  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1WMH\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	5.1
50°	2.0
52.5°	0.9
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)