

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296002

Luminaire Tested: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DL1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 398.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296002
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296002

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	76	76	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	73	73	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	67	67	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255308
5°	238190
10°	190800
15°	129513
20°	78383
25°	45825
30°	26105
35°	14348
40°	7614
45°	4000
50°	2320
55°	1759
60°	1491
65°	1557
70°	1475
75°	1271
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4000 cd/sqm



TEST NUMBER: P1296002

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	24.1
10°-20°	156.9	39.4
20°-30°	89.6	22.5
30°-40°	35.3	8.9
40°-50°	10.8	2.7
50°-60°	4.3	1.1
60°-70°	2.9	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	342.5	86.1
0°-40°	377.9	94.9
0°-60°	393.0	98.7
0°-90°	398.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1164	
5°	1082	96
15°	570	157
25°	189	90
35°	54	35
45°	13	11
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1296002
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1164.3
1°	1162.0
2°	1152.5
3°	1135.7
4°	1112.5
5°	1082.1
6°	1046.4
7°	1006.0
8°	959.3
9°	911.3
10°	856.9
11°	803.3
12°	744.4
13°	686.2
14°	626.4
15°	570.5
17.5°	442.4
20°	335.9
22.5°	252.2
25°	189.4
27.5°	140.4
30°	103.1
32.5°	74.5
35°	53.6
37.5°	38.0
40°	26.6
42.5°	18.3
45°	12.9
47.5°	9.1
50°	6.8
52.5°	5.3
55°	4.6
57.5°	4.2
60°	3.4
62.5°	3.0
65°	3.0
67.5°	2.7
70°	2.3
72.5°	1.9
75°	1.5
77.5°	1.1
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1296002
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)