

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296035

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296035
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296035
 CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132139
5°	128989
10°	119526
15°	106448
20°	91475
25°	77763
30°	64010
35°	49871
40°	35896
45°	22762
50°	13475
55°	9252
60°	8508
65°	7887
70°	7117
75°	6439
80°	6061
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22762 cd/sqm



TEST NUMBER: P1296035

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	9.8
10°-20°	130.2	23.4
20°-30°	147.1	26.5
30°-40°	116.4	20.9
40°-50°	58.8	10.6
50°-60°	23.5	4.2
60°-70°	15.1	2.7
70°-80°	8.3	1.5
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.6	59.6
0°-40°	448.0	80.6
0°-60°	530.3	95.4
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	603	
5°	586	54
15°	469	130
25°	321	147
35°	186	116
45°	73	59
55°	24	24
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1296035
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	602.6
1°	602.6
2°	600.5
3°	597.1
4°	592.2
5°	586.0
6°	578.4
7°	569.4
8°	559.7
9°	548.6
10°	536.8
11°	523.7
12°	511.2
13°	496.6
14°	482.8
15°	468.9
17.5°	430.1
20°	392.0
22.5°	356.0
25°	321.4
27.5°	287.5
30°	252.8
32.5°	220.3
35°	186.3
37.5°	155.2
40°	125.4
42.5°	97.7
45°	73.4
47.5°	54.7
50°	39.5
52.5°	29.8
55°	24.2
57.5°	22.2
60°	19.4
62.5°	17.3
65°	15.2
67.5°	13.2
70°	11.1
72.5°	9.7
75°	7.6
77.5°	6.2
80°	4.8
82.5°	3.5
85°	2.1
87.5°	0.7



TEST NUMBER: P1296035
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)