

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296045

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296045
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296045

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	9.8
10°-20°	130.2	23.4
20°-30°	147.1	26.5
30°-40°	116.4	20.9
40°-50°	58.8	10.6
50°-60°	23.5	4.2
60°-70°	15.1	2.7
70°-80°	8.3	1.5
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.6	59.6
0°-40°	448.0	80.6
0°-60°	530.3	95.4
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	603	
5°	586	54
15°	469	130
25°	321	147
35°	186	116
45°	73	59
55°	24	24
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1296045
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	602.6
1°	602.6
2°	600.5
3°	597.1
4°	592.2
5°	586.0
6°	578.4
7°	569.4
8°	559.7
9°	548.6
10°	536.8
11°	523.7
12°	511.2
13°	496.6
14°	482.8
15°	468.9
17.5°	430.1
20°	392.0
22.5°	356.0
25°	321.4
27.5°	287.5
30°	252.8
32.5°	220.3
35°	186.3
37.5°	155.2
40°	125.4
42.5°	97.7
45°	73.4
47.5°	54.7
50°	39.5
52.5°	29.8
55°	24.2
57.5°	22.2
60°	19.4
62.5°	17.3
65°	15.2
67.5°	13.2
70°	11.1
72.5°	9.7
75°	7.6
77.5°	6.2
80°	4.8
82.5°	3.5
85°	2.1
87.5°	0.7



TEST NUMBER: P1296045
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)