

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296049

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296049  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 619.0 lumens  
Efficiency: N/A  
Efficacy: 50.3 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296049  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296049

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147115
5°	143605
10°	133064
15°	118525
20°	101859
25°	86570
30°	71277
35°	55519
40°	39961
45°	25336
50°	15010
55°	10322
60°	9473
65°	8821
70°	7886
75°	7202
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25336 cd/sqm



TEST NUMBER: P1296049

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.5	9.8
10°-20°	144.9	23.4
20°-30°	163.8	26.5
30°-40°	129.5	20.9
40°-50°	65.4	10.6
50°-60°	26.2	4.2
60°-70°	16.8	2.7
70°-80°	9.2	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.2	59.6
0°-40°	498.7	80.6
0°-60°	590.4	95.4
0°-90°	619.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	619.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	671	
5°	652	61
15°	522	145
25°	358	164
35°	207	130
45°	82	65
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296049  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	670.9
1°	670.9
2°	668.6
3°	664.7
4°	659.3
5°	652.4
6°	643.9
7°	633.9
8°	623.1
9°	610.7
10°	597.6
11°	583.0
12°	569.1
13°	552.9
14°	537.5
15°	522.1
17.5°	478.9
20°	436.5
22.5°	396.4
25°	357.8
27.5°	320.0
30°	281.5
32.5°	245.2
35°	207.4
37.5°	172.7
40°	139.6
42.5°	108.7
45°	81.7
47.5°	60.9
50°	44.0
52.5°	33.2
55°	27.0
57.5°	24.7
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.7
70°	12.3
72.5°	10.8
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1296049  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1MW\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)