

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296053

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296053  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 623.0 lumens  
Efficiency: N/A  
Efficacy: 50.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296053  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296053

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.9	9.8
10°-20°	145.9	23.4
20°-30°	164.8	26.5
30°-40°	130.4	20.9
40°-50°	65.8	10.6
50°-60°	26.4	4.2
60°-70°	16.9	2.7
70°-80°	9.3	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.6	59.6
0°-40°	502.0	80.6
0°-60°	594.2	95.4
0°-90°	623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	623.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	675	
5°	657	61
15°	525	146
25°	360	165
35°	209	130
45°	82	66
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296053  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	675.2
1°	675.2
2°	672.9
3°	669.0
4°	663.6
5°	656.6
6°	648.1
7°	638.0
8°	627.1
9°	614.7
10°	601.5
11°	586.8
12°	572.8
13°	556.5
14°	541.0
15°	525.4
17.5°	482.0
20°	439.3
22.5°	398.9
25°	360.1
27.5°	322.1
30°	283.3
32.5°	246.8
35°	208.8
37.5°	173.9
40°	140.5
42.5°	109.4
45°	82.3
47.5°	61.3
50°	44.2
52.5°	33.4
55°	27.2
57.5°	24.8
60°	21.7
62.5°	19.4
65°	17.1
67.5°	14.7
70°	12.4
72.5°	10.9
75°	8.5
77.5°	7.0
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1296053  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)